



PlugTail® Connectors, Right Angle, Solid, 6-inch

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Large brass contacts snugly terminate on device blade terminals.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Available in any wire length up to 25 inches, use Configurable Solutions to order.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|--------------|
| Product Line | Pass & Seymour | UPC Number | 785007044553 |
| Country Of Origin | China | Application Sector | Commercial |
| Standard | cULus UL498 | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|-----------------|---|
| Dielectric Strength | Withstands 2000V minimum | Number of Wires | 3 |
|---------------------|--------------------------|-----------------|---|

| | | | |
|--------------------|---|--------------------------|-----------------------|
| Temperature Rating | Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact | Number of Poles | Double Pole |
| Wire Size | PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid, for use with PlugTail Receptacles only | Environmental Conditions | Flammability: UL94 V2 |
