

Project Name

Location

Prepared By



SATCO S11840

9WLED/GBL/4/CCT/RND/WH

Notes

[www] 05-16-2022 01:57:01

General

Status	Active
Wattage	9W
Voltage	120V
Finish	White
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Color Temperature	Warm to Cool White
Lumen Output	650L-750L
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	90
Beam Angle	36
Rated Hours	50000
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
Dimmable	Yes-Dimmable
Dimming Note	Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
IC Rated	Yes
Sloped Ceiling	Yes

Dimensions

Width (in.)	4.92
Height (in.)	1.42
Weight (lb.)	1.00

Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2393126
CA T20 / T24 Rationale	California T24 2016 & 2019 JA8 Compliant
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------