

GCM28CG3

by Burndy
Catalog ID: GCM28CG3

Prop 65 Notice

Mechanical Grounding Connector, #1 AWG (Sol)-4/0 AWG (Str), 1/4" Stud, Electro-Tinned



Product Details

General

| | |
|---------------------------------------|------------------------|
| Installation Torque Recommended in-lb | 45 lb-in |
| Material | Copper Alloy |
| Material Type - Screw | DURIUM™ Silicon Bronze |
| Physical Attribute - Screw Type | Hexagonal Bolt |
| Plated | N |
| Plating Type | Electro-Tinned |
| UPC | 781810421932 |
| UPC 12 Digit | 7818104219322 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - L Length Overall mm | 41 mm |
| Dimension - Length Overall inch | 1.62 in |
| Dimension - Width fraction | 2 in |
| Dimension - Width inch | 2.00 in |
| Dimension - Width mm | 51 mm |

Conductor Related

| | |
|-------------------------------------|---------------------------------------|
| Conductor - Copper Solid Size | 1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG |
| Conductor - Copper Solid Size Range | #1 AWG-4/0 AWG |
| Conductor - Copper Str Size | 1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG |
| Conductor - Copper Str Size Range | 1 AWG-4/0 AWG |

Certifications and Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 20 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)