



## Juno® RetroBasics™ LED Trim Kit

RetroBasics LED trim kits provide the most economical solution for efficiently lighting a space using LED technology with virtually zero maintenance. Available in 4" and 5/6" sizes, the RetroBasics downlight family covers an array of applications, providing a solution for every room of a home.

### Features and Benefits:

- **Sizes** – Available in 4" (up to 625 lumens) and 5/6" sizes (up to 850 lumens). Both are 90 CRI.
- **Switchable White Technology** – tactile slider switch integrated into trim allowing for easy color adjustments between 5 color temperature options (2700K, 3000K, 3500K, 4000K or 5000K).
- **Practical, Functional Design** – non-conductive thermal plastic trim ideal for dead front applications.
- **Low Profile Construction** – optimized for wider fixture spaces.
- **Easy Installation** – trim features a quick connect plug for easy electrical connection in seconds.
- **IC Rated** – for use with housings installed in direct contact with insulation.



# Juno® RetroBasics™ LED Trim Kits

## Ordering Information

### 4in Downlight

Ordering Example: RB4S SWW5 MW M6

Series	Color Temperature	Finish	Packaging
<b>RB4S</b> RetroBasics 4" Smooth	<b>SWW5</b> Switchable White (2700K, 3000K, 3500K, 4000K, 5000K)	<b>MW</b> Matte White	<b>M6</b> Master Pack - Individually boxed

### 5/6in Downlight

Ordering Example: RB56S SWW5 MW M6

Series	Color Temperature	Finish	Packaging
<b>RB56S</b> RetroBasics 5/6" Smooth	<b>SWW5</b> Switchable White (2700K, 3000K, 3500K, 4000K, 5000K)	<b>MW</b> Matte White	<b>M6</b> Master Pack - Individually boxed

Contractor Packs also available - Sold as 1 box with 6 units. Not individually boxed. Order as:

**RB4S SWW5 CP6 MW M2**

**RB56S SWW5 CP6 MW M2**



**Pairs perfectly with:**

**Juno® Quick Connect New Construction & Remodel LED Housings for a Complete Downlight Solution.**

Order housings separately



**QC New Construction Housing**

QC4, QC5, QC6



**QC Remodel Housing**

QC4R, QC5R, QC6R

