

STE403NP

ELECTRONIC THERMOSTAT – SINGLE PROGRAMMING

5750 W



PRACTICAL AND EFFICIENT!

The STE403NP electronic thermostat allows you to precisely control the temperature. It has a Security mode that lets you program a maximum temperature setpoint. It's simple and safe!



SIMPLE TO USE AND INSTALL



GREAT POWER

5750W @ 347V



INCREASED SAVINGS AND COMFORT

INCOMPARABLE ACCURACY



ELECTRICITY SAVINGS

ENERGY SAVINGS OF 10-15%
DEPENDING ON USE*

COLOR

- white

FINISH

- molded plastic

WATTAGE AND VOLTAGE

- 150 W to 2000 W @ 120 V
- 260 W to 3475 W @ 208 V
- 300 W to 4000 W @ 240 V
- 350 W to 4600 W @ 277 V
- 400 W to 5750 W @ 347 V

CONTROL

- acts like a programmable thermostat by automatically lowering the temperature once per 24-hour period (Single programming mode)
- compatible with forced-air units (Fan mode)

frost-free warning

- lock option at a maximum temperature setpoint (Security mode)
- display in Celsius or Fahrenheit

ACCURACY

- accurate ambient temperature control of ± 1 °F
- CSA C828-13
- temperature sensing with thermistor

TEMPERATURE RANGE

- 37 to 86 °F

WARRANTY

- three years

*independent study

TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	AMPERAGE	FREQUENCY
CODE	MINIMUM	MAXIMUM	VOLTS	AMPERES	Hz
STE403NPW24	150/260/300/350/400	2000/3475/4000/4600/5750	120/208/240/277/347	16.7	50/60

Dimensions: 4 1/2 in. wide, 4 7/8 in. high and 1 3/8 in. deep

°STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-color products.
For all the latest models and prices, please refer to our website at www.stelpro.com.

