

D070

REMOTE PLENUM THERMOSTAT – LOW VOLTAGE / 24 V

COLOUR

- off-white

VOLTAGE

- 1 A @ 24 Vac

CONTROL

- 2-wire connection
- compatible with CIR-048 used in duct heaters (SDHx series)

TEMPERATURE RANGE

- between -20 and 70 °C (-5 and 160 °F)

WARRANTY

- one year



PRODUCT	DESCRIPTION	PRICE
D070	remote plenum thermostat	47.00

Dimensions : 3.54 in. x 3.54 in. x 1.57 in. (89.9 mm x 89.9 mm x 39.9 mm)



ET120

ELECTRONIC THERMOSTAT – LOW VOLTAGE / 0-10 V

COLOUR

- off-white

VOLTAGE

- 24 Vac

CONTROL

- output: 0-10 V

TEMPERATURE RANGE

- between 10 and 32 °C (50 and 90 °F)
- display in Celcius only

WARRANTY

- one year



PRODUCT	DESCRIPTION	PRICE
ET120	0-10 V electronic thermostat (Celcius only)	108.00

Dimensions : 3.27 in. x 3.27 in. x 1.19 in. (83.1 mm x 83.1 mm x 30.2 mm)



°STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-colour products.
For all the latest models and prices, please refer to our website at www.stelpro.com.