

# FFI

## FLOOR INSERT FAN HEATER



### HEAT FROM AN UNEXPECTED PLACE

The FFI is the perfect solution when there's no wall space available, such as under low windows, bay windows and patio doors. It's also a great fit for offices, narrow entryways and bathrooms. It can be recessed between floor joists. Its grille is solidly constructed of rigid aluminum to withstand foot traffic. Installation at construction sites is easy thanks to its compact design. This floor insert fan heater can also be recessed into concrete floors.

#### DURABLE ALUMINUM GRILLE

#### EASILY CONCEALED

#### EASY INSTALLATION

#### CAN BE RECESSED INTO CONCRETE FLOORS

#### COLOURS

- **standard:** white, soft white
- **Orora (optional):** refer to [www.stelpro.com/en-CA/Orora](http://www.stelpro.com/en-CA/Orora)

#### FINISH

- epoxy-polyester powdercoat

#### MANUFACTURING

- durable 16-gauge steel cabinet and 9-gauge aluminum extruded grille
- protective wire mesh to prevent foreign objects from entering the interior of the unit
- 80 CFM capacity fan
- thermal protection with automatic reset

#### ELEMENT

- tubular element sheathed with spiral-wound fins for improved heat dissipation

#### CONTROL

- wall thermostat only (not included) – the use of an electronic thermostat is strongly recommended

#### INSTALLATION

- recessed between floor joists
- in a concrete floor without framing
- large wiring compartment

#### WARRANTY

- five years

#### IDEAL FOR:

in front of a patio door, office, narrow entryway, bathroom

# °STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-colour products. For all the latest models and prices, please refer to our website at [www.stelpro.com](http://www.stelpro.com).





## TECHNICAL SPECIFICATIONS

PRODUCT	POWER	VOLTAGE	THROW DISTANCE		HEAT RISE		WEIGHT		PRICE
CODE	WATTS	VOLTS	M	FT	°C	°F	KG	LB	
<b>FFI1002</b>	1000/750	240/208	2	6'5"	60	108	8.1	18	<b>610.00</b>
<b>FFI1502</b>	1500/1125	240/208	2	6'5"	66	119	8.1	18	<b>630.00</b>

Add W for white or SW for soft white (consult the optional colours chart or contact your Stelpro representative for all other colours).

## TECHNICAL DRAWINGS

