

STZW402 | KI™ Z-WAVE

ELECTRONIC THERMOSTAT FOR SMART HOME

4000 W



CONNECTED COMFORT

KI Z-Wave thermostats can easily be integrated into your home's **Z-Wave** network, so you can adjust the temperature setpoint of rooms in your home from a distance.

- INTEGRATES EASILY WITH A SMART HOME HUB**
- CONTROL WITH A MOBILE APPLICATION** DEPENDING ON THE HUB
- ELECTRICITY SAVINGS** ENERGY SAVINGS OF 10-15% DEPENDING ON USE*

COMPATIBILITY

- Z-Wave hub required
- Z-Wave Plus certified

COLOUR

- white

FINISH

- molded plastic

WATTAGE AND VOLTAGE

- 150 W to 2000 W @ 120 V
- 300 W to 4000 W @ 240 V

CONTROL

- two functions available: comfort and economy
- two- or four-wire connection
- outdoor temperature display[†]
- frost-free warning
- display in Celsius or Fahrenheit
- backlit screen with adjustable intensity

ACCURACY

- accurate ambient temperature control of $\pm 0.5^{\circ}\text{C}$ (1°F)
- CSA C828-13
- temperature sensing with thermistor

TEMPERATURE RANGE

- 5 to 30 $^{\circ}\text{C}$ (41 to 86 $^{\circ}\text{F}$)

WARRANTY

- three years

* independent study

† depending on the central controller and its application

COMPATIBLE WITH



For home automated system compatibilities and instructions on connecting to your KI thermostat, visit www.stelpro.com.

TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	AMPERAGE	FREQUENCY	PRICE
CODE	MINIMUM	MAXIMUM	VOLTS	AMPERES	Hz	
STZW402WB+	150/300	2000/4000	120/240	16.7	50/60	120.00

Dimensions: 4 7/8 in. (124 mm) wide, 4 7/8 in. (124 mm) high and 1 3/8 in. (29 mm) deep

°STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-colour products.
For all the latest models and prices, please refer to our website at www.stelpro.com.





Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. **No returns accepted on optional-colour products.**
For all the latest models and prices, please refer to our website at www.stelpro.com.