

# SORB | ORLÉANS™

## HIGH-END WALL FAN HEATER



ORLÉANS™



## FOR FAST COMFORT!

The Stelpro family of high-end Orléans convectors is growing. Treat yourself to our brand-new Orléans high-end fan heater and enjoy a toasty warm bathroom even in winter. Thanks to its optimum heat output and rapid temperature rise, this model provides heat exactly when you need it. It is also the quietest fan heater in its category, allowing you to relax and enjoy some peace and quiet. Very similar to our Orléans high-end convector, this fan heater has an optional built-in, smart-home-ready thermostat.

### THE QUIETEST FAN HEATER IN ITS CATEGORY

**HEAT "BOOST" MODE**  
FAST TEMPERATURE RISE  
(1000 W TO 2000 W)†

**STURDY, DURABLE  
AND RUST-RESISTANT**

**OPTIONAL BUILT-IN  
ELECTRONIC THERMOSTAT**  
PERFECT FOR THE SMART HOME

### COLOURS

- **standard:** white, soft white
- **Orora (optional):** refer to [www.stelpro.com/en-CA/Orora](http://www.stelpro.com/en-CA/Orora)

### FINISH

- epoxy-polyester powdercoat

### MANUFACTURING

- high performance polymer cabinet, 20-gauge satin-finish steel front with moulded aluminum edges
- centrifugal fan that ensures a quiet and efficient airflow
- thermal protections with manual reset
- top front air intake and bottom front air discharge

### ELEMENT

- high-quality nichrome element that generates instant heat

### CONTROL

MODEL WITHOUT A THERMOSTAT:

- an electronic wall thermostat is recommended

MODEL WITH A BUILT-IN THERMOSTAT:

- built-in smart thermostat featuring the Zigbee protocol (compatible with Allia and Maestro)
- 1000 W to maintain temperature setpoint
- 2000 W when "boost" mode is activated (with a timer)
- colour-code feedback for responsible energy consumption
- drastic temperature drop detection (open window function)

### INSTALLATION

- recessed or surface mounted – surface adaptor included
- on the wall, a minimum of 6 in. from the floor
- front easy to install with only one mounting screw
- power switch selector – 1000 W or 2000 W (model without a thermostat only)

### WARRANTY

- five years, \*three years on electronic components

† 5°C (9°F) temperature rise within five minutes. (Tests performed with the 2000 W model in a 70 ft² room.)

### IDEAL FOR:

bathroom, entrance, vestibule, hallway, living space

PART OF THE ORLÉANS FAMILY OF PRODUCTS

NEED A CONVECTOR?

SOR



# °STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-colour products. For all the latest models and prices, please refer to our website at [www.stelpro.com](http://www.stelpro.com).



FC\_SORB\_EN\_290722



## DISCOVER OUR RANGE OF COLOURS **ORORA**



MOSS GREEN



TURQUOISE



DENIM BLUE



MIDNIGHT BLUE



RED



CHARCOAL

All optional colours: [www.stelpro.com/en-CA/Orora](http://www.stelpro.com/en-CA/Orora)

## TECHNICAL SPECIFICATIONS

PRODUCT	WITH THERMOSTAT		WITHOUT THERMOSTAT	VOLTAGE	HEIGHT		LENGTH		WEIGHT		PRICE
	HEATING	HEAT "BOOST" MODE			MM	IN.	MM	IN.	KG	LB	
CODE	WATTS	WATTS	WATTS	VOLTS	MM	IN.	MM	IN.	KG	LB	
<b>SORB2002M</b>	1000/750	2000/1500	---	240/208	398	15 11/16	322	12 11/16	4.3	9.4	<b>636.00</b>
<b>SORB2002WC</b>	---	---	2000/1500 or 1000/750*	240/208	398	15 11/16	322	12 11/16	4.3	9.4	<b>494.00</b>

Add W for white or SW for soft white (consult the optional colour chart and contact your Stelpro representative for all other colours).

\* Selected when installed with a power switch

### BUILT-IN THERMOSTAT

CONTROL THE TEMPERATURE OF YOUR HOME FROM YOUR SMARTPHONE, TABLET OR COMPUTER



COMPATIBLE CONTROLLER REQUIRED

Compatible with



WORKS WITH SmartThings

For home automated system compatibilities and instructions on connecting to your thermostat refer to [www.stelpro.com](http://www.stelpro.com).

## TECHNICAL DRAWINGS

