

ST252NPFF – ST402NPFF

ELECTRONIC THERMOSTAT FOR FAN HEATERS

NON-PROGRAMMABLE



2500 W

4000 W



A WIND OF CHANGE!

Stelpro's all-new non-programmable electronic thermostats designed specifically for fan heaters let you make the most of your comfort thanks to advanced features such as "Boost" and "Lobby" modes. Harmonious design, superior technology and safe operation merge to ensure your comfort in all circumstances.

ENERGY SAVINGS UP TO 12%*

ECO MODE

ONE-CLICK TEMPERATURE SETBACK

HEAT "BOOST" FEATURE

RAPID TEMPERATURE RISE

LOBBY MODE

COMPENSATES FOR FAST TEMPERATURE DROPS

SAFE DESIGN

SEALED HOUSING

S³ MOUNTING PLATE

STURDY, SIMPLE AND SAFE INSTALLATION

COLOR

- white

FINISH

- molded plastic

WATTAGE AND VOLTAGE

ST252NPFF

- 150 W to 1250 W @ 120 V
- 260 W to 2160 W @ 208 V
- 300 W to 2500 W @ 240 V

ST402NPFF

- 150 W to 2000 W @ 120 V
- 260 W to 3475 W @ 208 V
- 300 W to 4000 W @ 240 V

CONTROL

- three-wire connection
- compatible with forced-air units
- eco mode: One-click temperature setback
- maximum power when "boost" mode is activated (with a timer)
- display in Celsius or Fahrenheit

ACCURACY

- accurate ambient temperature control of $\pm 1^{\circ}\text{F}$
- CSA C828-19
- temperature sensing with thermistor

TEMPERATURE RANGE

- 41 to 86 $^{\circ}\text{F}$

WARRANTY

- three years

*independent study

TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	MAX. AMPERAGE	FREQUENCY
	CODE	MINIMUM	MAXIMUM	AMPERES	HZ
ST252NPFF		150/260/300	1250/2160/2500	10.4	60
ST402NPFF		150/260/300	2000/3475/4000	16.7	60

DIMENSIONS ST252NPFF: 4,35 in. wide, 4,94 in. high and 1,38 in. deep
DIMENSIONS ST402NPFF : 4,94 in. wide, 4,94 in. high and 1,38 in. deep

°STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-color products.
For all the latest models and prices, please refer to our website at www.stelpro.com.



FC_ST252-ST402_NPFF_US_290722