

# ST402PFF

## ELECTRONIC THERMOSTAT FOR FAN HEATERS

PROGRAMMABLE



4000 W



### STAY IN TUNE WITH THE TIMES!

This new programmable electronic thermostat designed specifically for fan heaters lets you make the most of your comfort thanks to advanced features such as "Boost" and "Lobby" modes. With simple three-step programming, you can manage your home's comfort while enjoying energy savings up to 20% compared to a mechanical thermostat.

#### ENERGY SAVINGS UP TO 20%\*

#### SIMPLE THREE-STEP PROGRAMMING

#### HEAT "BOOST" FEATURE QUICK TEMPERATURE RISE

#### "LOBBY" MODE COMPENSATES FOR FAST TEMPERATURE DROPS

#### SAFE DESIGN SEALED HOUSING

#### S<sup>3</sup> MOUNTING PLATE STURDY, SIMPLE AND SAFE INSTALLATION

#### COLOR

- white

#### FINISH

- molded plastic

#### WATTAGE AND VOLTAGE

- 150 W to 2000 W @ 120 V
- 260 W to 3475 W @ 208 V
- 300 W to 4000 W @ 240 V

#### CONTROL

- three-wire connection
- maximum power when "boost" mode is activated (with a timer)
- possibility of four events on weekdays and two events on weekends
- protection against power failure (two hours)
- display in Celsius or Fahrenheit

#### ACCURACY

- accurate ambient temperature control of  $\pm 1^{\circ}\text{F}$
- CSA C828-19
- temperature sensing with thermistor

#### TEMPERATURE RANGE

- 41 to 86 °F

#### WARRANTY

- three years

\* independent study

### TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	MAX. AMPERAGE	FREQUENCY
CODE	MINIMUM	MAXIMUM	VOLTS	AMPERES	Hz
ST402PFF	150/260/300	2000/3475/4000	120/208/240	16.7	60

DIMENSIONS ST402PFF : 4,94 in. wide, 4,94 in. high and 1,38 in. deep

FC\_ST402\_PFF\_US\_280722

°STELPRO

°STELPRO reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. **No returns accepted on optional-color products.**  
For all the latest models and prices, please refer to our website at [www.stelpro.com](http://www.stelpro.com).

