

TH140-28-01-B

ELECTRONIC THERMOSTAT – LINE AND LOW VOLTAGE – 7-DAY PROGRAMMABLE

COLOR

- white

FINISH

- molded plastic

VOLTAGE

- Max: 5 A @ 24 V – 240 V resistive
- Max: 2 A @ 24 V – 240 V inductive

CONTROL

- versatile thermostat that controls systems from millivolts to 240 V and is also well-suited for hot water heating
- battery powered (2 AA alkaline batteries)
- terminals R, W (X, C optional remote input)
- temperature sensing with thermistor

TEMPERATURE RANGE

- 40 to 85°F

WARRANTY

- one year

PRODUCT	DESCRIPTION
TH140-28-01-B	ELECTRONIC PROG. THERMOSTAT, MILLIVOLT TO 240V, 5A RES. 2A IND.

Dimensions: 3 13/16 in. (97 mm) wide, 5 in. (127 mm) high and 1 in. (26 mm) deep



°STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-color products.
For all the latest models and prices, please refer to our website at www.stelpro.com.