


BS2M Series

200 A 600 V; oversize enclosure, subfeed on load side

Product specifications

- Conductor range: line: 6 AWG–250 kcmil, load: 12–1/0 AWG
- Aluminum tunnel type connector for line side
- For overhead service only
- Dual lug subfeed for load side
- Supplied with screw type ring
- Weatherproof Type 3R enclosure
- Primarily used in: All provinces



	Cat. no.	Description	Dimensions (in.)			Weight each	
			H	W	D	lb	kg
4 Jaw							
BS2M-V	BS2M-V	Overhead, hub opening	17 ⁷ / ₁₆	12	5 ⁷ / ₁₆	15	6.8



Diagrams

