



# CUT LEVEL 4 NITRILE DIPPED GLOVES

## MORE DURABLE. BETTER PROTECTION.

EN388



4X43D



EN388 STANDARDS						
Abrasion	1	2	3	4	-	-
Cut Resistance (Coup Test)	1	2	3	4	5	X*
Tearing	1	2	3	4	-	-
Puncture	1	2	3	4	-	-
Cut Resistance (TDM Test)	A	B	C	D	E	F

\*If the coupe test provides a 3 or above it is marked as an "X" for not applicable and uses the TDM 100 test instead

**SMARTWIPE™ Touch  
Screen Compatible  
Palms & Fingertips**

**High Dexterity  
Fingertips**

**Sandy  
Nitrile Grip**

**Light &  
Breathable Back**



**Color-Coded Bands  
Easy cut level  
identification**

SPECIFICATIONS	
Gauge	13
Liner Material	Nylon and HPPE Blend Knit
Dip Material	Sandy Nitrile
Cuff Style	Elasticated Knit

RECOMMENDED APPLICATIONS
<ul style="list-style-type: none"> <li>■ Duct &amp; Sheet Metal Work</li> <li>■ Concrete Work</li> <li>■ Tile Cutting</li> <li>■ Pipe Threading</li> <li>■ Wire Stripping</li> <li>■ Demolition</li> </ul>

CARE INSTRUCTIONS
Machine wash warm water (105°F), mild detergent, no bleach. Line dry.

SIZE	1 PAIR	12 PAIR (Contractor Pack)
S	48-22-8945	48-22-8945B
M	48-22-8946	48-22-8946B
L	48-22-8947	48-22-8947B
XL	48-22-8948	48-22-8948B
XXL	48-22-8949	48-22-8949B

**SEE  
MORE  
PPE**



or visit <https://qr.mke.tl/2qm6s>



Milwaukee

CUT LEVEL 4

SMARTSHIELD™

9 1/2" L  
48-22-8947

