

# **CUT LEVEL 2 WINTER INSULATED DIPPED GLOVES**

## ULTIMATE WARMTH. ALL DAY COMFORT.



2242B X1X

**EN511** 



EN388 STANDARDS						
Abrasion	1	2	3	4	-	-
Cut Resistance (Coup Test)	1	2	3	4	5	X*
Tearing	1	2	3	4	-	-
Puncture	1	2	3	4	-	-
Cut Resistance (TDM Test)	Α	В	С	D	Е	F

\*If the coupe test provides a 3 or above it is marked as an "X" for not applicable and uses the TDM 100 test instead

High Dexterity 15 Gauge Outer Liner

1/2 Double Dipped Latex Water resistance

Warm Acrylic Terry Liner

**Secure Dual Liner** 



10 Gauge Inner Liner

Breathable Back

Color-Coded Bands Easy cut level

Easy cut level identification

#### **SPECIFICATIONS**

Gauge	10 & 15	
Liner Material	Secure Dual Liner	
Dip Material	Double Latex 1/2 Dip	
Cuff Style	Elasticated Knit	

#### RECOMMENDED APPLICATIONS

- High-Dexterity Applications
- Light Material Handling
- Finish Carpentry
- Yard Maintenance
- Plumbing

### **CARE INSTRUCTIONS**

Machine wash warm water (105°F), mild detergent, no bleach. Line dry.

SIZE	1 PAIR	12 PAIR (Contractor Pack)
S	48-73-7920	48-73-7920B
М	48-73-7921	48-73-7921B
L	48-73-7922	48-73-7922B
XL	48-73-7923	48-73-7923B
XXL	48-73-7924	48-73-7924B







