

CUT LEVEL 5 WINTER INSULATED DIPPED GLOVES

ULTIMATE WARMTH. ALL DAY COMFORT.



EN511







EN388 STANDARDS						
Abrasion	1	2	3	4	-	-
Cut Resistance (Coup Test)	1	2	3	4	5	Х*
Tearing	1	2	3	4	-	-
Puncture	1	2	3	4	-	-
Cut Resistance (TDM Test)	А	В	С	D	E	F

*If the coupe test provides a 3 or above it is marked as an "X" for not applicable and uses the TDM 100 test instead



10 Gauge Inner Liner

Breathable Back

Color-Coded Bands Easy cut level identification

SPECIFICATIONS				
10 & 13				
Secure Dual Liner				
Double Latex 3/4 Dip				
Elasticated Knit				

EDECIEICATIONS

RECOMMENDED APPLICATIONS

- Duct & Sheet Metal Work
- Concrete Work
- Tile Cutting
- Pipe Threading
- Wire Stripping
- Demolition

CARE INSTRUCTIONS

Machine wash warm water (105°F). mild detergent, no bleach. Line dry.

SIZE	1 PAIR	12 PAIR (Contractor Pack)	
S	48-73-7950	48-73-7950B	
M	48-73-7951	48-73-7951B	
L	48-73-7952	48-73-7952B	
XL	48-73-7953	48-73-7953B	
XXL	48-73-7954	48-73-794B	

SEE MORE PPE





or visit https://qr.mke.tl/2qm6s

