

Project Name

Location

Prepared By



SATCO S9676

100W/LED/HID/40K/100-277V EX39

Notes

[www] 06-09-2021 01:41:25

General

Status	Discontinued
Substitute	S39676
Watts	100W
Incandescent Equivalent	500W
Fluorescent Equivalent	150W
HID Equivalent	400W
Volts	100V-277V
Shape	Corncob
Base	Mogul Extended
ANSI Base	EX39
Finish	Clear
CCT (Kelvin)	4000
Temperature	Cool White
CRI	80+
Lumens	13000L
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Corncob
Technology	LED
Min Compartment Size	Length: 17.3 in. Width: 9.25 in. Depth: 9.25 in.
Ballasting Requirements	Ballast Bypass-Direct wire only 100-277V

Electrical

Working Voltage	AC 90-305V
Operating Frequency	50/60 Hz
Power Factor	0.95
Burning Position	Universal
Surge Protection	Built-in surge protection
Operating Temperature	-20C (-4F) to a maximum of +65C (+149F)

Physical

MOL	9.63
MOD	5.88
Lens Finish	Clear
Housing Color	White

Additional Information

Includes	Safety chain
Rated For Enclosed Fixture	Yes
IP Rating	IP65
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PFNR9J3E; PM8Q4J33
California Status	Lawful for sale

RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
<http://www.satco.com/>

