

SWT

MECHANICAL THERMOSTAT – LINE VOLTAGE

COLOURS

- white, soft white

FINISH

- molded plastic

VOLTAGE

- 22 A @ 120-277 Vac
- 1/2 hp

CONTROL

- two-wire connection (single pole model) or four-wire connection (double pole model)
- temperature in degrees Celsius
- off position (double pole model)

TEMPERATURE RANGE

- 10 to 30 °C (50 to 90 °F)

WARRANTY

- one year



PRODUCT	DESCRIPTION	PRICE
SWT1C*	SINGLE POLE THERMOSTAT (CELSIUS)	19.00
SWT2C	DOUBLE POLE THERMOSTAT (CELSIUS)	27.00

*Add SW for soft white.
Dimensions: 2 29/32 in. (74 mm) wide, 4 37/64 in. (116 mm) high and 1 9/64 in. (29 mm) deep



RJ32

MECHANICAL THERMOSTAT – LINE VOLTAGE

COLOUR

- white

VOLTAGE

- 22 A @ 120, 208 or 240 Vac / 19 A @ 277 Vac

CONTROL

- two-wire connection (single pole model) or four-wire connection (double pole model)
- temperature in degrees Celsius

TEMPERATURE RANGE

- 5 to 32 °C (41 to 90 °F)

WARRANTY

- one year



PRODUCT	DESCRIPTION	PRICE
RJ32W1	SINGLE POLE THERMOSTAT	23.00
RJ32W2	DOUBLE POLE THERMOSTAT	32.00

Dimensions: 4 1/2 in. (114.3 mm) wide, 2 3/4 in. (69.9 mm) high and 2 1/4 in. (57.2 mm) deep



°STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-colour products.
For all the latest models and prices, please refer to our website at www.stelpro.com.