

TG511A1000

UNIVERSAL THERMOSTAT GUARD

MANUFACTURING

- clear plastic
- compatible with all thermostats sold by Stelpro
- features a tumbler lock (keys included)
- can be installed without removing the thermostat from the wall

- protection against vandalism, damage and unauthorized tampering of settings

WARRANTY

- one year



PRODUCT	DESCRIPTION
TG511A1000	UNIVERSAL THERMOSTAT GUARD

Inside dimensions: 6 1/16 in. x 5 1/16 in. x 2 15/16 in.



KEYS (INCLUDED)

The ambient temperature can only be changed by the key owner.



F29

THERMOSTAT GUARD

MANUFACTURING

- clear plastic (F290143) or metal (F290193)
- compatible with the STCNP, STCP, STE302R2+, STE241, T822K1034, T87K1015, D010 and ET180 thermostats
- features a tumbler lock (keys included)

- protection against vandalism, damage and unauthorized tampering of settings

WARRANTY

- one year



F290143



F290193

PRODUCT	DESCRIPTION
F290143	CLEAR PLASTIC THERMOSTAT GUARD
F290193	METAL THERMOSTAT GUARD

Inside dimensions: F290143: ring base of 3 1/2 in. x 6 3/8 in. x 3 1/4 in., solid base of 3 1/2 in. x 6 3/8 in. x 3 in. F290193: 3 13/16 in. x 6 in. x 3 1/8 in.



KEYS (INCLUDED)

The ambient temperature can only be changed by the key owner.



FD60M

MECHANICAL TIMER

COLOR

- white

VOLTAGE

- 20 A @ 120 Vac / 10 A @ 240 and 277 Vac

INSTALLATION

- wall mounted with wall plate (not provided)

CONTROL

- 60-minute timer
- used to control forced-air units such as: SK, RWF, SKS

WARRANTY

- one year



PRODUCT	DESCRIPTION
FD60MCW70	60-MINUTE TIMER

Dimensions: 1.6 in. x 2.79 in. x 1.19 in.



STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-color products. For all the latest models and prices, please refer to our website at www.stelpro.com.