



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V Circuit Breakers - Type BL, 2-Pole, 120/240VAC are Circuit Protection Molded Case Circuit Breakers. Type: BLH Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120/240V Amperage Rating: 15A Trip Range: Thermal Magnetic Interrupt Rating: 22 AIC Number Of Poles: 2P

General technical data	
number of poles	2
suitability for operation	Electrical Distribution
Electricity	
continuous current rated value	15 A
Model	
product brand name	Siemens
type of electrical connection	BOLT-ON
Mechanical Design	
depth [in]	4 in
design of the product	BLH
height [in]	4 in
width [in]	2 in
General product approval	
standard	UL 489

last modified:

12/20/2023

