

Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V AFCI Circuit Breakers - 2-Pole, AFCI - BAFH, 22KAIC, 120/240VAC are Circuit Protection Molded Case Circuit Breakers. Sub Brand: N/A Type: BAFH Special Features: CAFCL Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120/240V Amperage Rating: 20A Load Rating: N/A Frequency Rating: N/A Phase: N/A Frame: N/A Trip Type: N/A Trip Range: Thermal Magnetic Interrupt Rating: 22AIC Number Of Poles: 2P

number of poles	2
suitability for operation	Electrical Distribution
<b>Electricity</b>	
continuous current rated value	20 A
<b>Model</b>	
product brand name	SIEMENS
special product feature	CAFCL
type of electrical connection	PLUG-IN
<b>Mechanical Design</b>	
depth [in]	3 in
design of the product	BAFH
height [in]	3.5 in
material of the enclosure	COMPOSITE
width [in]	2 in
<b>General product approval</b>	
standard	UL 489

last modified:

1/6/2021 

