



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V Circuit Breakers - Type BL, 3-Pole, 240VAC are Circuit Protection Molded Case Circuit Breakers. Type: HBL Application: Electrical Distribution Standard: UL 489 Voltage Rating: 240V Amperage Rating: 40A Trip Range: Thermal Magnetic Interrupt Rating: 65 AIC Number Of Poles: 3P

| | |
|---------------------------------|-------------------------|
| number of poles | 3 |
| suitability for operation | Electrical Distribution |
| Electricity | |
| continuous current rated value | 40 A |
| Model | |
| product brand name | SIEMENS |
| type of electrical connection | BOLT-ON |
| Mechanical Design | |
| depth [in] | 3 in |
| design of the product | HBL |
| height [in] | 3 in |
| width [in] | 3 in |
| General product approval | |
| standard | UL 489 |

last modified: 1/7/2021 

