



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V Circuit Breakers - Type BL, 3-Pole, 240VAC are Circuit Protection Molded Case Circuit Breakers. Type: BLH Application: Electrical Distribution Standard: UL 489 Voltage Rating: 240V Amperage Rating: 70A Trip Range: Thermal Magnetic Interrupt Rating: 22 AIC Number Of Poles: 3P

number of poles	3
suitability for operation	Electrical Distribution
<b>Electricity</b>	
continuous current rated value	70 A
<b>Model</b>	
product brand name	SIEMENS
type of electrical connection	BOLT-ON
<b>Mechanical Design</b>	
depth [in]	4 in
design of the product	BLH
height [in]	3 in
width [in]	4 in
<b>General product approval</b>	
standard	UL 489

last modified: 1/6/2021

