



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V AFCI Circuit Breakers - 1-Pole AFCI Combo BAFH 22KAIC 120/240VAC are Circuit Protection Molded Case Circuit Breakers. Sub Brand: N/A Type: BL Special Features: N/A Application: Electrical Distribution Standard: UL 1699 Voltage Rating: 120V Amperage Rating: 20A Load Rating: N/A Frequency Rating: N/A Phase: N/A Frame: N/A Trip Type: N/A Trip Range: Thermal Magnetic Interrupt Rating: 65 AIC Number Of Poles: 1P

number of poles	1
suitability for operation	Electrical Distribution
<b>Electricity</b>	
continuous current rated value	20 A
<b>Model</b>	
product brand name	SIEMENS
type of electrical connection	BOLT-ON
<b>Mechanical Design</b>	
depth [in]	1.2 in
design of the product	BL
height [in]	5.3 in
width [in]	3.3 in
<b>General product approval</b>	
standard	UL 1699

last modified: 1/6/2021 

