



Siemens Low Voltage Molded Case Circuit Breakers General Purpose MCCBs are Circuit Protection Molded Case Circuit Breakers. 1-Pole circuit breaker type BQH. Rated 120V (060A) (AIR 22 kA). Special features: Load side lugs are included.

number of poles	1
suitability for operation	Electrical Distribution
<b>Electricity</b>	
continuous current rated value	60 A
<b>Model</b>	
product brand name	SIEMENS
type of electrical connection	BOLT-ON
<b>Mechanical Design</b>	
depth [in]	4 in
design of the product	BQ
height [in]	1 in
width [in]	3 in
<b>General product approval</b>	
standard	UL 489

last modified: 1/6/2021 

