



Siemens Low Voltage Molded Case Circuit Breakers General Purpose MCCBs - Type BQ, 2-Pole, 120/240VAC are Circuit Protection Molded Case Circuit Breakers. 2-Pole Common-Trip circuit breaker type BQH. Rated 120/240V (125 A) (AIR 22 kA). Special features: Load side lugs are included.

number of poles	2
suitability for operation	Electrical Distribution
Electricity	
continuous current rated value	25 A
Model	
product brand name	SIEMENS
type of electrical connection	BOLT-ON
Mechanical Design	
depth [in]	3 in
design of the product	BQ
height [in]	4 in
width [in]	2 in
General product approval	
standard	UL 489

last modified:

1/6/2021 

