

Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches. CSA 600A  
2P 3W 240V FUSED HD TYPE 1

General technical data	
fastening method	SURFACE
number of poles	2
suitability for operation	DISCONNECTING MEAN FOR SERVICE ENTRANCE / LOADS
Electricity	
ampacity	600 A
Environmental conditions	
ambient temperature during operation maximum	85 °C
ambient temperature during operation minimum	-29 °C
Model	
product brand name	SIEMENS
product sub brand name	VBII
product type designation	HEAVY DUTY SWITCH
type of electrical connection	MECHANICAL LUGS
Mechanical Design	
design of the actuating element	SINGLE THROW
material	STEEL
General product approval	
certificate of suitability	UL98 / CSA

last modified:

7/18/2024 

