

SIEMENS LOW VOLTAGE MOLDED CASE CIRCUIT BREAKER WITH THERMAL - MAGNETIC TRIP. QR FRAME STANDARD 40C BREAKER. 150A 3-POLE (65KA AT 240V). SPECIAL FEATURES: NO LUGS INSTALLED.

General technical data	
suitability for operation	Circuit Protection
Electricity	
voltage between phase and Ground (GND) rated value	240 V
voltage between phase and phase rated value	240 V
Model	
product brand name	Siemens
product feature	QR 250A 240V Breakers
special product feature	QR 250A 240V Breakers
Mechanical Design	
design of the product	General Purpose MCCBs

last modified:

2/4/2021 

