

SIEMENS LOW VOLTAGE MOLDED CASE CIRCUIT BREAKER WITH THERMAL - MAGNETIC TRIP. QR FRAME STANDARD 40C BREAKER. 225A 3-POLE (65KA AT 240V). SPECIAL FEATURES: NO LUGS INSTALLED.

| General technical data         |                                        |
|--------------------------------|----------------------------------------|
| number of poles                | 3                                      |
| suitability for operation      | CIRCUIT PROTECTION                     |
| Model                          |                                        |
| product brand name             | Siemens                                |
| product feature                | FIELD INSTALLABLE INTERNAL ACCESSORIES |
| special product feature        | FIELD INSTALLABLE INTERNAL ACCESSORIES |
| type of electrical connection  | LOAD LUGS                              |
| Mechanical Design              |                                        |
| design of the overload release | THERMAL MAGNETIC                       |
| design of the product          | CIRCUIT BREAKER                        |
| material of the enclosure      | MOLDED CASE CIRCUIT BREAKER            |
| size of the circuit-breaker    | QR FRAME                               |
| General product approval       |                                        |
| standard                       | UL 489/CSA 22.2                        |

last modified:

2/4/2021 

