



Siemens Low Voltage Residential Circuit Breakers Miniature Thermal Mag Circuit Breakers - Type QP/MP 1-pole 10k are Circuit Protection Load Center Mains, Feeders, and Miniature Circuit Breakers. Type: QP/MP Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120V Amperage Rating: 25A Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: 1P

number of poles	1
suitability for operation	Electrical Distribution
Electricity	
continuous current rated value	25 A
Model	
product brand name	SIEMENS
type of electrical connection	PLUG-IN
Mechanical Design	
depth [in]	12.8 in
design of the product	QP/MP
height [in]	3.5 in
width [in]	3.4 in
General product approval	
standard	UL 489

last modified: 1/6/2021 

