



Siemens Low Voltage Residential Circuit Breakers Miniature Thermal Mag Circuit Breakers - Type QP/MP, 2-Pole, 120/240VAC are Circuit Protection Load Center Mains, Feeders, and Miniature Circuit Breakers. Type: QP/MP Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120/240 V Amperage Rating: 100A Trip Range: Thermal Magnetic Interrupt Rating: 22 AIC Number Of Poles: 2P

number of poles	2
suitability for operation	Electrical Distribution
<b>Electricity</b>	
continuous current rated value	100 A
<b>Model</b>	
product brand name	SIEMENS
type of electrical connection	PLUG-IN
<b>Mechanical Design</b>	
depth [in]	3 in
design of the product	QP/MP
height [in]	3 in
width [in]	2 in
<b>General product approval</b>	
standard	UL 489

last modified: 1/6/2021

