



Siemens Low Voltage Residential Circuit Breakers Miniature Circuit Breakers AFCI - Combo AFCI 2-pole plug-on 10k and 22k are Circuit Protection Load Center Mains, Feeders, and Miniature Circuit Breakers. Type: QAFH Application: Electrical Distribution Standard: UL 1699 Voltage Rating: 120/240 V Amperage Rating: 15A Trip Range: Thermal Magnetic Interrupt Rating: 22 AIC Number Of Poles: 2P Connection: PLUG-IN Length: 3 Width: 2 Height: 3

number of poles	2
suitability for operation	Electrical Distribution
Electricity	
continuous current rated value	15 A
Model	
product brand name	SIEMENS
type of electrical connection	PLUG-IN
Mechanical Design	
depth [in]	3 in
design of the product	QAFH
height [in]	3 in
width [in]	2 in
General product approval	
standard	UL 1699

last modified: 1/6/2021 

