



Siemens Low Voltage Residential Circuit Breakers Miniature Thermal Mag Circuit Breakers - Type QP/MP, 3-Pole, 240VAC are Circuit Protection Load Center Mains, Feeders, and Miniature Circuit Breakers. Type: QP/MP Application: Electrical Distribution Standard: UL 489 Voltage Rating: 240V Amperage Rating: 70A Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: 3P

number of poles	3
suitability for operation	Electrical Distribution
<b>Electricity</b>	
continuous current rated value	70 A
<b>Model</b>	
product brand name	SIEMENS
type of electrical connection	PLUG-IN
<b>Mechanical Design</b>	
depth [in]	12.8 in
design of the product	QP/MP
height [in]	3.4 in
width [in]	3.8 in
<b>General product approval</b>	
standard	UL 489

last modified: 1/6/2021 

