



Siemens Energy Management Residential Specialty Load centers: small circuit (2-10). Sub Brand: Load Centers Type: 1: Application: Residential: Voltage Rating: 120/240V Amperage rating: 60A Phase: 1PH Load regulation: 60A Wiring configuration: 3w Bus Rating: 60A Interrupt Rating: 100000AIC. OUTDOOR EQ LC 2S 4C ML 60A

General technical data	
configuration of the busbars	60A
fastening method	Surface
product function note	
phase number	1
suitability for operation	Residential
Electricity	
ampacity	60 A
voltage between phase and Ground (GND) rated value	120 V
voltage between phase and phase rated value	240 V
Breaking Capacity	
switching capacity current according to EN 60898 rated value	100000 A
Model	
product brand name	Siemens
product type designation	1
type of wiring of distribution board	3w
Mechanical Design	
number of modular width units for installation width	2
width [in]	1386.45 in

last modified:

10/23/2025 

