

A19 Energy Saver



A19

Order code	Description	Watts (W)	Base	Volts (V)	Lumens output (lm)	Average life (hrs)	Finish	Operating position	Incan. equivalent (W)	Case qty (master)
A19										
62795 ^{1,2}	H43/A19/CL/120V/STD	43	E26	120	750	1 000	Clear	Universal	60	100
62796 ^{1,2}	H53/A19/CL/120V/STD	53	E26	120	1 050	1 000	Clear	Universal	75	100
62799 ^{1,2}	H43/A19/FR/120V/STD	43	E26	120	750	1 000	Frost	Universal	60	100
62801 ^{1,2}	H72/A19/FR/120V/STD	72	E26	120	1 490	1 000	Frost	Universal	100	100

JC & JD



JC (G4)



T3 (BA15d)



T3 (E11)

Order code	Description	Watts (W)	Base	Volts (V)	Lumen output (lm)	Average life (hrs)	Finish	Case qty (inner/master)
JC (G4)								
51129	H10JC/CL/2M/G4/12V/STD	10	G4	12	130	2 000	Clear	100/1 000
51130	H20JC/CL/2M/G4/12V/STD	20	G4	12	300	2 000	Clear	100/1 000
67786	H20JC/CL/2M/G4/24V	20	G4	24	350	2 000	Clear	25/100
T3 (BA15d)								
69281	H75T3/CL/2M/BA15D/120V	75	BA15d	130	1 050	2 000	Clear	12/120
69245	H100T3/CL/2M/BA15D/130V/STD S2	100	BA15d	130	1 600	2 000	Clear	50/500
50883	H150T3/CL/2M/BA15D/130V/STD	150	BA15d	130	3 000	2 000	Clear	12/120
50885	H250T3/CL/2M/BA15D/130V/STD	250	BA15d	130	4 800	2 000	Clear	12/120
T3 (E11)								
69239	H50T3/CL/2M/E11/130V/STD S2	50	E11	130	1 120	2 000	Clear	50/500
69240	H75T3/CL/2M/E11/130V/STD S2	75	E11	130	1 350	2 000	Clear	50/500
69241	H100T3/CL/2M/E11/130V/STD S2	100	E11	130	1 800	2 000	Clear	50/500
69243	H250T3/CL/2M/E11/130V/STD S2	250	E11	130	4 800	2 000	Clear	50/500

¹This product is affected by provincial Energy Efficiency Regulations in Ontario, Quebec & British Columbia. Note that it will remain available until stock is depleted.



JD & JCD



JD (G9 Glass Base)



JD (G9 Ceramic Base)



JCD (GY6.35)



JCD (G8)



JCD (GY8)

Order code	Description	Watts (W)	Base	Volts (V)	Lumen output (lm)	Average life (hrs)	Finish	Case qty (inner/master)
JD (G9) - Glass Base								
58260	H25JD/42mm/CL/2M/G9/130V/STD	25	G9	130	255	2 000	Clear	12/120
57259	H40JD/42MM/CL/2M/G9/130V/STD	40	G9	130	480	2 000	Clear	12/120
57256	H40JD/42MM/F/2M/G9/130V/STD	40	G9	130	480	2 000	Frost	12/120
57255	H50JD/42MM/CL/2M/G9/130V/STD	50	G9	130	600	2 000	Clear	12/120
57258	H60JD/42MM/CL/2M/G9/130V/STD	60	G9	130	800	2 000	Clear	12/120
58258	H75JD/42mm/CL/2M/G9/130V/STD	75	G9	130	1 050	2 000	Clear	12/120
JD (G9) - Ceramic Base								
55057	H25JD/56MM/CL/2M/G9/120V/STD	25	G9	120	255	2 000	Clear	12/120
11247	H50JD/56MM/CL/2M/G9/120V/STD	50	G9	120	600	2 000	Clear	12/120
JCD (GY6.35)								
51045	H20JCD/CL/2M/GY6.35/120V/STD	20	GY6.35	120	180	2 000	Clear	12/120
50879	H35JCD/CL/2M/GY6.35/120V/STD	35	GY6.35	120	380	2 000	Clear	12/120
50878	H50JCD/CL/2M/GY6.35/120V/STD	50	GY6.35	120	600	2 000	Clear	12/120
10317	H75JCD/CL/2M/GY6.35/120V/STD	75	GY6.35	120	1 050	2 000	Clear	12/120
JCD (G8)								
55055	H20JCD/CL/2M/G8/120V/STD	20	G8	120	200	2 000	Clear	12/120
15710	JCD100W/130V/G8	100	G8	130	1 600	2 000	Clear	12/120
JCD (GY8)								
11267	H75JCD/CL/2M/GY8/120V	75	GY8	120	1 300	2 000	Clear	10/50



Xenon JD



MOL: 2 15/32 in. (63 mm)
Ø 23/32 in. (18 mm)

T3 (BA15d)



MOL: 2 1/4 in. (57 mm)
Ø 23/32 in. (18 mm)

T3 (E11)



MOL: 2 5/16 in. (59 mm)
Ø 23/32 in. (18 mm)

T3 (E12)



MOL: 1 25/32 in. (45 mm)
Ø 23/32 in. (18 mm)

T3 (E12)

Order code	Description	Watts (W)	Base	Volts (V)	Lumen output (lm)	Average life (hrs)	Finish	Case qty (inner/master)
T3 (BA15d)								
60956	X60T3/2M/BA15D/120V/STD	60	BA15d	120	960	2 000	Clear	12/120
T3 (E11)								
60954	X60T3/2M/E11/120V/STD	60	E11	120	960	2 000	Clear	12/120
T3 (E12)								
60948	X20T3/2M/E12/120V/STD	20	E12	120	200	2 000	Clear	12/120
T3 (E12)								
60949	X20T3/F/2M/E12/120V/STD	20	E12	120	200	2 000	Frost	12/120
60953	X40T3/F/2M/E12/120V/STD	40	E12	120	560	2 000	Frost	12/120



dimmable UV stop

J Type Double Ended



T3 - 79 mm



T3 - 119 mm



T3 - 256 mm

Order code	Description	Watts (W)	Base	Volts (V)	Lumen output (lm)	Average life (hrs)	Finish	Case qty (inner/master)
T3 - 79 mm								
68200	H60T3/79mm/CL/2M/R7S/130V/STD	60	R7s	130	800	2 000	Clear	12/120
69250	H75T3/79mm/2M/R7S/120V/STD S2	75	R7s	120	750	2 000	Clear	50/500
55047	H75T3/79mm/CL/2M/R7S/130V/JPN/STD	75	R7s	130	1 150	2 000	Clear	12/480
69251	H100T3/79MM/2M/R7S/120V/STD S2	100	R7s	120	1 300	2 000	Clear	50/500
69252	H100T3/79mm/2M/R7S/130V/STD S2	100	R7s	130	1 300	2 000	Clear	50/500
57224	H150T3/79mm/2M/R7S/120V/STD	150	R7s	120	2 400	2 000	Clear	12/120
69253	H150T3/79mm/2M/R7S/130V/STD S2	150	R7s	130	2 400	2 000	Clear	50/500
T3 - 119 mm								
69255	H100T3/119mm/2M/R7S/130V/STD S2	100	R7s	130	1 300	2 000	Clear	50/500
69256	H150T3/119mm/2M/R7S/130V/STD S2	150	R7s	130	1 800	2 000	Clear	50/500
69257	H200T3/119mm/2M/R7S/130V/STD S2	200	R7s	130	3 400	2 000	Clear	50/500
69259	H300T3/119mm/CL/2M/R7S/130V/STD S2	300	R7s	130	5 950	2 000	Clear	50/500
69260	H500T3/119mm/CL/2M/R7S/120V/STD S2	500	R7s	120	10 500	2 000	Clear	50/500
69261	H500T3/119mm/CL/2M/R7S/130V/STD S2	500	R7s	130	10 500	2 000	Clear	50/500
T3 - 190 mm								
51046	H1000T3/190mm/CL/2M/R7S/130V/STD	1 000	R7s	130	21 000	2 000	Clear	12/120
T3 - High Voltage								
59261	H300QT3/119mm/CL/2M/220V/STD	300	R7s	220	33 000	2 000	Clear	12/120
51047	H1000T3/190mm/CL/2M/R7S/240V/STD	1 000	R7s	240	21 000	2 000	Clear	12/120
51085	H1000T3/256mm/CL/2M/R7S/240V/STD	1 000	R7s	240	21 000	2 000	Clear	12/120
59262	H1500QT3/256mm/CL/2M/R7S/208V/STD	1 500	R7s	208	33 000	2 000	Clear	12/120
69279	H1500T3/256mm/CL/2M/R7S/240V	1 500	R7s	240	33 000	2 000	Clear	12/120
59260	H1500QT3/256mm/CL/2M/277V/STD	1 500	R7s	277	33 000	2 000	Clear	12/120
T3 - Low Voltage								
55088	H150T3/79mm/2M/R7S/12V/STD	150	R7s	12	2 900	2 000	Clear	10/100
10318	H300T3/119mm/CL/2M/R7S/24V/STD	300	R7s	24	5 400	2 000	Clear	10/100
10319	H300T3/119mm/CL/2M/R7S/32V/STD	300	R7s	32	5 400	2 000	Clear	10/100
T3 - Infrared								
55077	H375T3/221mm/CL/IR/5M/R7S/120V/STD	375	R7s	120	N/A	5 000	Clear	1/84
55070	H500T3/221MM/CL/IR/5M/R7S/120V/STD	500	R7s	120	N/A	5 000	Clear	1/25
55072	H1000T3/351MM/CL/IR/5M/ML/240V/STD	1 000	Metal Leads	240	N/A	5 000	Clear	1/25
55074	H1600T3/503MM/CL/IR/5M/ML/240V/STD	1 600	Metal Leads	240	N/A	5 000	Clear	1/25
55076	H3800T3/1062MM/CL/IR/5M/ML/570V/STD	3 800	Metal Leads	570	N/A	5 000	Clear	1/25

