



# GBM26T4

by Burndy  
Catalog ID: GBM26T4

Prop 65 Notice

Mechanical Grounding Connector, Cable to 1/4" - 1/2" Thick Bar, 4 AWG (Sol)-2/0 AWG (Str), 3/8" Stud.

## Product Details

### General

|                                       |                        |
|---------------------------------------|------------------------|
| Installation Torque Recommended in-lb | 240 lb-in              |
| Material                              | Copper Alloy           |
| Material Type - Screw                 | DURIUM™ Silicon Bronze |
| Physical Attribute - Screw Type       | Hexagonal Bolt         |
| Plated                                | N                      |
| Plating Type                          | Unplated               |
| UPC                                   | 781810111000           |
| UPC 12 Digit                          | 7818101110000          |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 24 mm    |
| Dimension - Length Overall inch | 0.94 in  |
| Dimension - Width fraction      | 1-1/3 in |
| Dimension - Width inch          | 1.34 in  |
| Dimension - Width mm            | 34 mm    |

### Conductor Related

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| Conductor - Copper Solid Size Range | #4 AWG-2/0 AWG                       |
| Conductor - Copper Str Size         | 4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG |
| Conductor - Copper Str Size Range   | 4 AWG-2/0 AWG                        |

### Certifications and Compliance

|                                         |       |
|-----------------------------------------|-------|
| Certification - CSA Approved            | Yes   |
| Certification - ETL                     | No    |
| Certification - UL Listed Direct Burial | Yes   |
| Certification - UL Recognized           | No    |
| Certification - cULus                   | No    |
| Industry Standard(s)                    | UL467 |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | CM    |
| UL Listed                               | Yes   |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)