

DRAWING NO.
SC212515-01

4





3

2

1

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
N	10/24/2015 00:00:00 AM	UPDATE CL501, CL501TN, AND KIT SALES DRAWINGS.	41982	MK	RR

FIELD WIRING USE #14-4 AWG CU; SOL. OR STR.	
CONDUCTOR SIZE	TIGHTENING TORQUE
14-10 AWG	20 INCH-LBS
8 AWG	25 INCH-LBS
6-4 AWG	35 INCH-LBS



NOTES:

- MATERIAL: BODY - TIN PLATED COPPER
SCREW - 300 SERIES OR 18-8 STAINLESS STEEL.
- SEE ITEM NUMBER: 50061563 FOR INSTALLATION INSTRUCTIONS AND RATINGS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS
AND ARE FOR REFERENCE ONLY.
- UL LISTED AND CSA CERTIFIED GROUNDING AND BONDING EQUIPMENT AND RATED
FOR DIRECT BURIAL IN CONCRETE OR EARTH.
UL LISTED GROUND LUGS AND DEVICES FOR USE WITH PHOTOVOLATAIC MODUELES AND PANELS.
CL501TN AND CL501TNBULK ARE THE SAME CONNECTOR, SUFFIX "BULK" DENOTES BULK PACKAGING.

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

LAY-IN LUG, COPPER	
ITEM NO: 10028448, 10107305	
CAT. NO: CL501TN, CL501TNBULK	
DRAWN BY: M KATHIR 10/28/15	
CHECKER: R ROMAN 12/22/15	
DSN APPVL: R ROMAN 12/22/15	
MFG APPVL: --	
QA APPVL: C KOWALCZYK 12/16/15	
MKT APPVL: P THERRIEN 12/22/15	
PROD FAM: MECHANICAL GROUNDING	DRAWING NO
PROJECT #: --	SIZE
DOCUMENT TYPE: Sales	C
REL LEVEL: Released	N

BURNDY

SCALE: 3:1	REV
SC212515-01	N
SHEET 1 OF 1	