



## GAR1826TN

by Burndy  
Catalog ID: GAR1826TN

Prop 65 Notice

Ground Clamp Copper Tin plated 4 AWG-2/0 AWG Installation Torque  
Recommended Run in-lb240 LB in

## Product Details

### General

Installation Torque Recommended Run in-lb	240 Lb-in
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin plated
U Bolt Type	257
UPC	621945145023
UPC 12 Digit	6219451450233

### Dimensions

Dimension - B Length inch	2.75 in
Dimension - Height inch	4.25 in
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.56 in
Dimension - Outside Diameter inch	2.38 in
Dimension - Width inch	3.69 in
Dimension - Width mm	94 mm

### Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	5-2/0
Conductor - Copper Tube Std Size	2
Conductor - Copper Tube Std Size Range	2
Conductor - Pipe or Round Tube Size Range	2 in
Conductor - Rod Size	2 in-2.38 in
Conductor - Rod Size Range	2-2 1/4

Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> <li>• CU Tube Std-Size</li> <li>• Rod-Size</li> </ul>
----------------	--

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### BURNDY Headquarters

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)