




REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	01/27/2012 00:00:00 AM	CREATE SALES DRAWING	26605	TS	MA



- NOTES:
- APPROXIMATE AMP RATING: 1500A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
 - DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

3 SUFFIX "TN" DENOTES TIN PLATED FERRULES.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES:		ITEM NO: 30019958	3
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: B23G24G23TN	
CANADA:		DRAWN BY: M. RAMESH 09/20/11	8" BURNDY
1-800-361-6975 (QUEBEC)		CHECKER: E. MARTIN 01/24/2012	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APPVL: E. MARTIN 01/24/2012	SCALE: 3:8
FOR PRODUCT INFO: http://www.burndy.com		MFG APPVL: --	
		QA APPVL: A. PINEDA 01/27/2012	DRAWING NO
		MKT APPVL: P. THERRIEN 01/24/2012	
		PROD FAM: CM&R	REV
		PROJECT #: --	
		DOCUMENT TYPE: Sales	A
		REL LEVEL: Released	