

DRAWING NO.
30021754

4

3

2

1

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	10/28/2011 00:00:00 AM	DRAWING RELEASED	26013	MA	JG

D

D

C


C

B

B

A

A



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
- APPROXIMATE AMP RATING: 360 INDOOR, 430 OUTDOOR
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- CERTIFIED TO CSA C22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

BRAID			
ITEM NO: 30021361			
CAT. NO: BF36N1			
DRAWN BY:	M. AYYAPPAN	10/28/11	BURNDY
CHECKER:	E. MARTIN	10/31/11	
DSN APPVL:	E. MARTIN	10/31/11	
MFG APPVL:	R. CRUZ	11/04/11	
QA APPVL:	A. PINEDA	11/01/11	
MKT APPVL:	P. THERRIEN	10/28/11	SCALE: 1:1
PROD FAM:	--	DRAWING NO	REV
PROJECT #:	--	30021754	A
DOCUMENT TYPE:	Sales	SHEET 1 OF 1	
REL LEVEL:	Released		