



GCM30

by Burndy
Catalog ID: GCM30

Prop 65 Notice

Mechanical Grounding Connector, 2 Copper Cables to 1/4" Thick Bar, 4 AWG (Str.) - 300 kcmil, 1/2" Stud

Product Details

General

Installation Torque Recommended in-lb	480 lb-in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
UPC	781810278017
UPC 12 Digit	7818102780177

Dimensions

Dimension - Height inch	2.00 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - Width fraction	2-1/5 in
Dimension - Width inch	2.21 in
Dimension - Width mm	56 mm

Conductor Related

Conductor - Copper Solid Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	4 AWG - 300 KCMIL
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil
Conductor - Copper Str Size Range	4 AWG-300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)