



BB100L106D34G15TN

by Burndy
Catalog ID: BB100L106D34G15TN

Flexible Copper Braid with Tin Plated Ferrules

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Plated	Y
UPC	781810508305
UPC 12 Digit	7818105083055

Dimensions

Dimension - L Length Overall mm	2701 mm
Dimension - Length Overall inch	106.34 in

Electrical Ratings

Amperage Rating	290 A
-----------------	-------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)