



## GQ2626

by Burndy  
Catalog ID: GQ2626

Prop 65 Notice

Cu Ground Connector, #4 - 2/0 AWG Str Cu , 6" IPS, Cable to Tube

## Product Details

### General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	400;291
UPC	781810239209
UPC 12 Digit	7818102392099

### Dimensions

Bolt Size	1/2 in
Dimension - Height inch	3.72 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5.00 in
Dimension - Width inch	2.44 in
Dimension - Width mm	62 mm

### Conductor Related

Conductor - Copper Str Size Range	4-2/0
Conductor Size	#4 AWG Str - 2/0 AWG Str
Conductor Type	<ul style="list-style-type: none"> <li>• CU Tube Std-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

UL Listed	Yes
-----------	-----

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)