



GK2129

by Burndy
Catalog ID: GK2129

Prop 65 Notice

Mechanical grounding connector; 3 cables to rod or pipe; 2/0 AWG Solid - 250 kcmil; 3-1/2" Pipe; 3-1/2" to 4" Rod; 1/2" Stud; UL467

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	781810196281
UPC 12 Digit	7818101962811

Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.50 in
Dimension - Height inch	6.16 in
Dimension - Width fraction	6-5/7 in
Dimension - Width inch	6.72 in
Dimension - Width mm	171 mm

Conductor Related

Conductor - Rod Size	3 1/2 in; 4 in
Conductor Size	2/0 AWG Sol - 250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)