

## GK6429TN



by Burndy  
Catalog ID: GK6429TN

Prop 65 Notice

IPS: 3/8" ROD: 5/8 - 3/4" CABLE: 2/0 SOL. - 250kcmil

### Product Details

#### General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Electro Plated
Type	Three Cables to Rod or Tube
UPC	781810079201
UPC 12 Digit	7818100792011

#### Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.63 in
Dimension - Height inch	2.88 in
Dimension - Width fraction	3-1/2 in
Dimension - Width inch	3.50 in
Dimension - Width mm	89 mm

#### Conductor Related

Conductor - Rod Size	5/8 in ; 3/4 in
Conductor Size	2/0 AWG Sol - 250 kcmil

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

#### Logistics

**For further technical assistance, please contact us****BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)