



DRAWING NO. SE212372-01		
CATALOG NUMBER	ITEM NUMBER	L
BD8NI	10011851	8.00 [203]
BD12NI	001693	12.00 [305]
BD14NI	30021459	14.00 [356]
BD15NI	25015041	15.00 [381]
BD16D50NI	50004605	16.50 [419]
BD18NI	26002396	18.00 [457]
BD24NI	001694	24.00 [610]
BD25D25NI	10060678	25.25 [641]
BD27NI	26000057	27.00 [686]
BD36NI	002153	36.00 [914]
BD48NI	25020209	48.00 [1219]
BD60NI	25020210	60.00 [1524]
BD180NI	10063818	180.00 [4572]



NOTES:

- FINISH: ADDED CATALOG NUMBER FOLLOWED BY "TN" TO INDICATE TIN PLATED FERRULES.
ADD CATALOG NUMBER FOLLOWED BY "W" TO INDICATE HOT TIN DIPPED FERRULES.
ADD CATALOG NUMBER FOLLOWED BY "SV" TO INDICATE SILVER PLATED FERRULES.
ADD CATALOG NUMBER FOLLOWED BY "NK" TO INDICATE NICKEL PLATED FERRULES.
- APPROXIMATE AMP RATING: 190 INDOOR, 225 OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

- ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- ALL SIZES ARE LISTED TO CSA C22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.
- BRAID SIZES MAY BE DESIGNATED BY SUFFIXES REPRESENTING VARIATIONS IN LENGTH, QUANTITY & SIZE OF MOUNTING HOLES, PAD SIZE AND FINISH. (REF. NOTES 4, 5)



BRAID, FLEXIBLE			
ITEM NO: SEE TABLE			
CAT. NO: BD--NI (TABLE)			
DRAWN BY: P.LAPONIUS 11/18/99			
CHECKER: J.WALTERS 11/18/99			
DSN APPVL: J.MICHAUD 11/17/99			
MFG APPVL: -- --			
QA APPVL: J.BRODEUR 11/17/99			
MKT APPVL: D.WALTERS 11/17/99			
SCALE: 1:1		DRAWING NO	
PROD FAM: MECHANICAL GROUNDING		REV	
PROJECT #: --		SIZE	
DOCUMENT TYPE: Sales		C	
REL LEVEL: Released		G	