




REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	10/29/2012	RELEASE SALES DRAWINGS OF THE AFFECTED ITEMS	29186	MS	MB



NOTES:

1. APPROXIMATE AMP RATING: 820A INDOOR, 980A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 50009680	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: B3F15G73	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DRAWN BY: N.D.KANNAN 10/11/2012	
		CHECKER: T.REYNOLDS 11/29/2012	
		DSN APRVL: R.CRUIZ 11/30/2012	
		MFG APRVL: --	
		QA APRVL: J.MEDINA 11/30/2012	
		MKT APRVL: K.ROBICHEAU 11/30/2012	
		PROD FAM: MECHANICAL GROUNDING	
		PROJECT #: --	
		DRAWING NO: 50009682	
		REV: A	
		DOCUMENT TYPE: SALES	
		REL LEVEL: Released	
		SIZE: B	
		SHEET 1 OF 1	