

GG182TN



by Burndy
Catalog ID: GG182TN

Prop 65 Notice

Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 2"-2 3/8" Pipe, 4.06 in Width. Tin Plated

Product Details

General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast, Tin Plated
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Electro Plated
U Bolt Type	230
UPC	781810416754
UPC 12 Digit	7818104167544

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Width inch	4.06 in
Dimension - Width mm	103 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)