



GP1629W

by Burndy
Catalog ID: GP1629W

Prop 65 Notice

GROUND CONNECTOR RUN, IPS 1-1/4", ROD: 1-3/8" to 1-1/2", COPPER
CABLE: 2/0 SOL - 250 kcmil, 70mm² STR - 120mm² STR, TORQUE: 240
LB-IN, Nm 27.0; Tin Plated

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Tin Plated Copper Alloys
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Hot Dipped
U Bolt Type	204
UPC	781810485613
UPC 12 Digit	7818104856133

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	1.88 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - Width fraction	3 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - Rod Size Range	1 3/8" - 1 1/2"
Conductor Size	2/0 AWG Sol - 250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	8
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)