



GXW6C58

by Burndy
Catalog ID: GXW6C58

Prop 65 Notice

Accom: Groove A: #12 SOL - #6 STR Groove B: 5/8" Stl Rod

Product Details

General

Material	Copper Alloy
Plated	N
Plating Type	Unplated
Trade Name	GROUNDWEJ™
UPC 12 Digit	0

Dimensions

Dimension - B Length inch	1.80 in
Dimension - Pad Width inch	3.30 in

Conductor Related

Conductor - Copper Solid Size A	12;11;10;9;8;7;6
Conductor - Copper Str Size A	12;10;9;8;7;6
Conductor - Rod Size	5/8
Conductor Type	• CU C Str-Size A • CU C Solid-Size A • CU C Str-Size B • CU C Solid-Size B • Rod-Size B

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)